

Il nuovo codice sarà fornito solo ad esaurimento del vecchio
 The new code will be supplied only when the old will be out of stock
 Der neue Kode wird nur angegeben, wenn der alte nicht mehr lieferbar ist
 Le nouveau code sera fourni uniquement lorsque le vieux stock sera écoulé
 El nuevo código será suministrado sólo cuando se agoten las existencias del antiguo
 O novo código irá ser fornecido apenas quando o antigo esgotar stock

* F_{1i} = Isothermal end force at 100% Cu
 ** F_{1p} = Polytrophic end force at 100% Cu



ACTIVE SAFETY



| N ₂ | | 0 - 80 °C 32 - 176 °F | ΔP ± 0,33 %/°C | P max 200 bar 2900 psi | P min 20 bar 290 psi | S 15,90 cm ² 2.464 in ² | SPM ~ 40 - 80 (at 20°C) | Max Speed 1,6 m/s 62.9 in/s | Maintenance kit 39BMMML03000C | |
|-----------------------------|----------------|--------------------------|---------------------------|------------------------------|----------------------------|---|-------------------------------|-----------------------------------|----------------------------------|------------|
| CODE | NEW | Cu | L | L min | F ₀ | F _{1i} * | F _{1p} ** | V ₀ | | PED |
| PHASING OUT from 05/2019 | | mm inch | mm inch | mm inch | Initial force daN lb | End force * daN lb | End force ** daN lb | cm ³ in ³ | ~Kg ~lb | 2014/68/EU |
| ML3000-015-C-N | ML3000-015-D-N | 15 0.59 | 120 4.72 | 105 4.13 | 3180 7149 | 4461 10029 | 5023 11291 | 105 6.40 | 1,67 3.68 | ✓ |
| ML3000-025-C-N | ML3000-025-D-N | 25 0.98 | 140 5.51 | 115 4.53 | ± 5% | 5013 11270 | 5781 12997 | 136 8.27 | 1,80 3.97 | ✓ |
| ML3000-038-C-N | ML3000-038-D-N | 38 1.50 | 170 6.69 | 132 5.20 | 200 bar 2900 psi | 5362 12054 | 6269 14094 | 184 11.22 | 2,00 4.41 | ✓ |
| ML3000-050-C-N | ML3000-050-D-N | 50 1.97 | 200 7.87 | 150 5.91 | | 5491 12344 | 6452 14505 | 233 14.24 | 2,20 4.85 | ✓ |
| ML3000-063-C-N | ML3000-063-D-N | 63 2.48 | 230 9.06 | 167 6.57 | | 5658 12720 | 6690 15039 | 282 17.19 | 2,40 5.29 | ✓ |
| ML3000-080-C-N | ML3000-080-D-N | 80 3.15 | 270 10.63 | 190 7.48 | +20 °C +68 °F | 5793 13023 | 6882 15472 | 347 21.14 | 2,66 5.86 | ✓ |

SERVICE BOX

code: 39SKML03000A


Seal (1x)

Washer (6x)

Screw (3x)

Instructions

! Sostituire ogni 1.000.000 di cicli. Remplacez à chaque million de cycles. Reemplazar cada 1 millón de ciclos. Nach 1 Mio. Hübe austauschen. Substituir a cada 1 milhão de ciclos.



HOW TO ORDER
 p. 167

INSTALLATION GUIDELINE
 p. 205